

# Commercial Specifications & Usage Chart

## Extend-A-Life™ Ethylene Absorption Filter Model 350



### USAGE RECOMMENDATIONS

For use in walk-in refrigerators/cold rooms up to 3,000 cubic feet in hospitals, schools, restaurants, hotels, florist shops, food service companies, military food service operations, super markets, and catering businesses. Also for use in refrigerated warehouses, refrigerated trailers, and shipping containers. Simply attach to the blower air intake or just hang in the overhead of the walk-in refrigerator, directly in the air-flow of the refrigerator unit.

### SPECIFICATIONS

Filter Dimensions: 18" L x 11/16" W x 5 3/4" H  
Case Pack Twelve (12) filters) per case

Case Weight: 28 lbs.  
Case Dimensions: 24" L x 12 1/2" W x 11" H  
Filter Weight: 2 lbs. each filter

### ADDITIONAL RECOMMENDATIONS

For Cold Rooms up to 3,000 cubic feet: No installation required. Place next to the air intake side of the refrigerator or just hang inside the cooler. Change every 30 – 60 days, depending upon density and type of inventory, change every 30 – 60 – 90 days.

For Shipping by Reefer Trucks or in Sea Containers: Place near the blower unit in the front of the container, If the container is using an air chute, then hang at the back of the container with a loading bar.

**PLACE THE FILTERS BETWEEN PALLETS OF PRODUCT. THE FILTERS ARE MOST EFFECTIVE WHEN AIR CAN FREELY PASS THROUGH THEM.**

If shipping a product in (7) days, use (1) filter per container  
If shipping from (7) to (14) days, use (2) to (3) per container.  
If shipping from (14) to (21) days, use (3) to (4) filters per container.  
Throw away filters upon arrival.  
Landfill Disposable